

Printronix Auto ID Guide Specification
RFID Label
860-960 MHz EPC Class 1, Gen 2
Alien 9630/9730/9830 Squiglette Antenna



Applicable Printer Models

SL4M/SL5000r MP2 Std Pitch, SL4M/T6 Short Pitch and T6 On Pitch

Disclaimer

Notwithstanding anything to the contrary in this document, the guidelines, suggestions and other information included in this document or otherwise provided to the recipient, including the guidelines and suggestions for developing converted RFID labels, are provided by Printronix Auto ID on an "as is" basis and without warranty of any kind whatsoever, expressed or implied. In particular, Printronix Auto ID disclaims any implied warranty of merchantability or fitness for a particular purpose. Printronix Auto ID will not be liable under any circumstances for any damages or losses related in any way to use of the guidelines, specifications or other information, including damages, which may be incurred as a result of labels not working properly in a specific application. All specifications are subject to change without notice. Testing of the converted labels in the printer is recommended prior to production quantities.

10/24/2016

Scope

This document provides guide specifications for constructing UHF Class 1, Gen 2, RFID labels with an Alien 9630/9730 or 9830 Squiglette RFID Gen2 Antenna for use with Printronix Auto ID RFID SL4M and SL5000r MP2 Std Pitch or SL4M, T6 Short Pitch or T6 On Pitch printers.

Requirements

Inlay Characteristics

Inlay: **Alien 9630 Squiglette**. Silicon Type: **Alien Higgs 3**. TID: **E2003412**.

Alien 9730 Squiglette. Silicon Type: **Alien Higgs 4**. TID: **E2003414**.

Alien 9830 Squiglette. Silicon Type: **Alien Higgs EC**. TID: **E2003811**.

Nominal operating frequency: **860-960 MHz**.

EPC Memory: **Alien 9630 Squiglette**. 96 up to 256 bits

Alien 9730 Squiglette. 128 bits.

Alien 9830 Squiglette. 128 bits.

User Memory: **Alien 9630 Squiglette**. 320 up to 512 bits set automatically based on EPC memory settings.

Alien 9730 Squiglette. 128 bits.

Alien 9830 Squiglette. 128 bits.

EPC Protocol: **UHF Class 1, Gen 2**

Printer Support and Setup

SL4M/SL5r MP2 Std Pitch & SL4M Short Pitch Antenna Position: **Yellow**

T6 Short Pitch and T6 On Pitch Antenna Position: **5**

SL4M & SL5r MP2 Std Pitch & SL4M Short Pitch RFID menu Tag Type: “**Alien9630 Sqlet**”

SL4M & SL5r MP2 Std Pitch & SL4M Short Pitch RFID menu Tag Type: “**Alien9730 Sqlet**”

T6 Short Pitch RFID menu Tag Type: “**Aln9630 ShortPitch**”

T6 Short Pitch RFID menu Tag Type: “**Aln9730 ShortPitch**”

T6 Short Pitch RFID menu Tag Type: “**Aln9830 ShortPitch**”

T6 On Pitch RFID menu Tag Type: “**Aln9630 OnPitch**”

T6 On Pitch RFID menu Tag Type: “**Aln9730 OnPitch**”

T6 On Pitch RFID menu Tag Type: “**Aln9830 OnPitch**”

SL4M/SL5r MP2 Std Pitch RFID menu (Interim Tag Type: “**Avery AD230**”).

SL4M Short Pitch RFID menu (Interim Tag Type: “**Alien9630 Sqlet**”).

T6 Short Pitch RFID menu (Interim Tag Type: “**N/A**”).

SL4M MP2 Std Pitch RFID menu Tag Position: **0.0 inches**


SL4M and T6 Short Pitch RFID menu Tag Position: - **0.2 inches**

T6 On Pitch RFID menu Tag Position: - **0.8 inches**

Interim Tag Type selection works with 96 bit EPC only. Printer firmware update is required to work with full memory.

Contact Information

For comments or questions, please contact Andy Edwards at AEdwards@PrintronixAutoID.com or 657-258-0816.



Label Side View



Label Direction
Through Printer


**Printronix Auto ID RFID Label Requirements for SL4M/SL5r “Std Pitch”
MP2 Gen 2 Alien 9630/9730 Squiglette Inlay**

Not to Scale
All Dimensions in Inches

Oct 24, 2016

Figure 1. Label Layout






Printronix Auto ID RFID Label Requirements for SL4M/T6 “Short Pitch”
Alien 9630/9730/9830 Squiglette Inlay

Not to Scale
All Dimensions in Inches

Oct 24, 2016

Figure 2. Label Layout



Printronix Auto ID RFID Label requirements for T6 "On Pitch"
 Alien 9630/9730/9830 Squiglette Inlay

Not to Scale
 All Dimensions in Inches

Oct 24, 2016

Figure 3. Label Layout